
Brondell®

Swash[®] LT89 Advanced Bidet Toilet Seat with Side Arm Control

Models: LT89-EW, LT89-RW



Features

Warm Water Washes

Fully Adjustable Water Temperature and Pressure

Heated Toilet Seat with 4 Warmth Levels

LED Nightlight with On/Off Function

Self-Cleaning, Stainless Steel Nozzle

Five Nozzle Positions

Nozzle Oscillation, Gentle, Pulse, and Strong Wash Modes

Side-Arm Control Panel

Gentle-Close Seat and Lid

Quick Release Seat

1-Year Limited Warranty

Technical Specifications

recimical specifications	
Power Voltage / Frequency	120 V / 60 Hz
Max Power Consumption	870 W
Power Cord Length	46.8" / 118.87 cm
Rated Power Source	120 V
Seat Weight Limit	330 lbs / 149.69 kg
Lid Weight Limit	160 lbs / 72.57 kg





Brondell, Inc. PO Box 470085 San Francisco, CA 94147 brondell.com

Brondell®

Weight and Dimensions	
Dimensions (L x W x H)	Elongated: 20.7" x 18.5" x 5.7" / 52.58 cm x 47 cm x 14.48 cm Round: 19.5" x 18.5" x 5.7" / 49.53 cm x 47 cm x 14.48 cm
Seat Thickness	1.4" / 3.56 cm
Bidet Hose Length	25″ / 63.5 cm
Weight	Elongated: 11.24 lbs / 5.1 kg Round: 10.8 lbs / 5 kg

Warm Water Washing Device	
Supply Water Pressure	9.95 psi-106.7 psi / 0.07 MPa-0.73 MPa
Incoming Water Temperature	37.4°F-104°F / 3°C-104°C
Flow Rate	Rear Wash: 0.13-0.21 gal/min / 0.5 L/min-0.79 L/min Front Wash: 0.13-0.18 gal/min / 0.5L/min-0.68 L/min Strong Wash: 0.13-0.16 gal/min / 0.5-0.6 L/min
Default Cycle Time	Rear Wash: 2 Minutes; Front Wash: 2 Minutes; Strong Wash: 2 Minutes
Water Pressure Control	5 Levels
Water Temperature Control	4 levels: OFF - Incoming Water Temp.; Low - 91.4°F / 33°; Medium - 96.8°F / 36°C, High - 102.2°F / 39°C
Max Heater Power Consumption	800 W
Safety Devices	Thermal Fuse, Thermostat, Water Level Sensor, Thermal Sensor, Bi-metal

Heated Seat and Air Dryer	
Seat Temperature Control	4 levels: OFF - Room Temp; Low - 93.2°F / 34°C; Medium -100.4°F / 38°C; High - 107.6°F / 42°C
Max Seat Heater Power Consumption	55 W
Safety Devices	Thermostat, Thermal Fuse, Thermal Sensor, Seat Occupied Sensor

Get the right fit.

- A. Measure the distance between the front of your toilet bowl and the center of the bolt holes
 Elongated: 18"–19.5" / 45.7 cm–49.5 cm
 Round: 16"–17.75" / 40.6 cm–45.1 cm
- B. The distance from the center of the bolt holes to the toilet tank must be at least 1.5" / 3.81 cm.
 If the distance is less than 1.5 inches, the seat may extend slightly over the front edge of your toilet bowl.
- C. Distance between bolt holes 5.25"-7.45" / 13.33 cm-18.92 cm
- D. Measure the distance from the front of the toilet tank to the front of the toilet bowl
 If this measurement is 20" / 50.8 cm inches or more, purchase an elongated seat.

 If this measurement is less than 20" / 50.8 cm, purchase a round seat.

